

Data Sheet

Cable gland set 1 set(s) : 201pcs



Thread	Cable range (ømm)	Aperture (ømm)	Thread length (mm)	Gland pcs.	Locknut pcs.	Cap pcs.
M12*1.5	3.0~6.5	12	8	15	15	15
M16*1.5	4.0~8.0	16	8	15	15	15
M18*1.5	5.0~11.0	18	8	10	10	10
M20*1.5	6.0~12.0	20	9	9	9	9
M22*1.5	10.0~14.0	22	10	6	6	6
M25*1.5	13.0~18.0	25	10	4	4	4
M32*1.5	16.0~20.0	32	11	4	4	4
M40*1.5	22.0~32.0	40	13.7	2	2	2
M50*1.5	32.0~38.0	50	14	2	2	2

Material: PP

Color: White

Thread type: M

Operating & storage temperature: -20~+ 80 °C