









Data Sheet





powered
by 

Contact Blocks (SA□ -C□ □)

Model	Contact	Features	Applied switches	Appearance
SA-CAM	A contact (normally open)	<ul style="list-style-type: none"> Modular type Ring / Fork terminal available Modular connection (up to 3 units) 	Ø 22/25 mm, Ø 30 mm, □ 30 mm Control switches	
SA-CBM	B contact (normally closed)			
SA-CA	A contact (normally open)	<ul style="list-style-type: none"> Singular type (dust-resistant contact point) Fork terminal available Loose screw prevention 		
SA-CB	B contact (normally closed)			

Power supply / current	110 VAC~ / 10 A, 250 VAC~ / 6 A
Dielectric strength	2,500 VAC~ 50/60 Hz for 1 minute
Insulation resistance	≥ 1,000 MΩ (500 VDC= megger)
Contact resistance	≤ 20 mΩ (initial)
Electrical life cycle	≥ 100,000 operations (20 operations/min)
Contact material	AgNi10
Approval	CE    
Weight	Modular type: ≈ 10 g, Singular type: ≈ 11 g

Data Sheet

LED Blocks (SA□ -L□ □)				
Model	Power supply	Features	Applied switches	Appearance
SA-LD□ M	AC/DC voltage type 12-24 VAC~ 50/60 Hz 12-24 VDC==	<ul style="list-style-type: none"> • Modular type • Ring / Fork terminal available • Modular connection (up to 3 units) 	Ø 22/25 mm, Ø 30 mm, □ 30 mm Control switches, Pilot lights	
SA-LA□ M	AC voltage type 110-220 VAC~ 50/60 Hz			
SA-LD□	AC/DC voltage type 12-24 VAC~ 50/60 Hz 12-24 VDC==	<ul style="list-style-type: none"> • Singular type (dust-resistant contact point) • Fork terminal available • Loose screw prevention 		
SA-LA□	AC voltage type 110-220 VAC~ 50/60 Hz			

• □ : Color (R: Red / B: Blue / G: Green / Y: Yellow / W: White)

■ Removal

Separate the unit using a flat-head (-) screwdriver.



Data Sheet

Item No.	Model
2465053	SA-CA
2465054	SA-CAM
2465055	SA-CB
2465056	SA-CBM
2465057	SA-LD
2465058	SA-LDM
2465059	SA-LA
2465060	SA-LAM
2465061	SA-LAB
2465062	SA-LAG
2465063	SA-LAR
2465064	SA-LAY
2465065	SA-LABM
2465066	SA-LAGM
2465067	SA-LARM
2465068	SA-LAYM
2465069	SA-LDBM
2465070	SA-LDGM
2465071	SA-LDRM
2465072	SA-LDYM
2465073	SA-LDR
2465674	SA-LDG
2465074	SA-LDY
2465075	SA-LDB