

## tesa® Ultra Power Clear Repairing Tape - 56496, 56497

tesa® Ultra Power Clear Repairing Tape is a special-purpose tape that, due to its transparency, allows for unobtrusive repairs. Its strong adhesive makes it stick to various surfaces, including slightly rough ones. The tape is hand-tearable and thick, making it ideal for quick and lasting repairs. The tape is a great choice under extreme weather conditions due to its UV- and temperature resistance.

### Main Application

- Ideal for patching large holes, cracks, gaps and tears
- Ideal for invisible repairs on transparent plastic material
- To fix cracks in glass
- Sticks also on slightly rough and textile surfaces

### Technical Data & Properties

<b>Dimensions</b>	10 m x 48 mm; 20 m x 48 mm
<b>Backing</b>	Polyethylene
<b>Total thickness</b>	170 µm
<b>Adhesive</b>	Synthetic rubber
<b>Adhesion to steel</b>	8.5 N/cm
<b>Adhesion to glass</b>	10.0 N/cm
<b>Adhesion to PE</b>	5.0 N/cm
<b>Adhesion to PVC</b>	5.5 N/cm
<b>Elongation at break</b>	100%
<b>Tensile strength</b>	35 N/cm
<b>Temperature resistance (short term)</b>	Min. -10 °C; Max. +90 °C
<b>UV-Resistance</b>	6 months

- |                       |     |                    |      |
|-----------------------|-----|--------------------|------|
| • Abrasion resistance | ●●● | • Water resistance | ●●●● |
| • Initial Tack        | ●●● | • Hand-tearability | ●●●● |

Evaluation across relevant tesa® assortment: very good ●●●●      good ●●●      medium ●●      low ●

**For the latest information on this product please visit <http://www.tesa.com/consumer>**

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

## Additional Information & Pictures

### Features

- Transparent
- Weather-resistant
- UV-resistant
- Highly temperature resistant
- Conformable to any shape or object
- Hand-tearable
- Easy to unwind



For the latest information on this product please visit <http://www.tesa.com/consumer>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.