

tesa® Ultra Power Extreme Repairing Tape - 56622, 56623

tesa® Ultra Power Extreme Repairing Tape is a multi-purpose repairing tape with a high tensile strength and very strong adhesion to almost any surface, even rough ones. It provides a remarkable ease of use due to its flexibility. The tape is a great choice under extreme weather conditions due to its UV- and temperature resistance.

Main Application

- Ideal for patching large holes, cracks, gaps and tears
- Ideal for repairing broken parts
- To repair small damages on bumpers

Technical Data & Properties

Dimensions	10 m x 50 mm; 25 m x 50 mm
Backing	PET-cloth laminated with Polyethylene-film
Total thickness	420 µm
Adhesive	Natural rubber
Adhesion to steel	11.0 N/cm
Adhesion to glass	10.0 N/cm
Adhesion to PE	6.0 N/cm
Adhesion to PVC	7.5 N/cm
Elongation at break	20 %
Tensile strength	60 N/cm
Temperature resistance (Short-term)	min. -15 °C; max. +90 °C

- | | | | |
|-----------------------|------|--------------------|------|
| • Abrasion resistance | ●●●● | • Water resistance | ●●●● |
| • Initial Tack | ●●●● | • Hand-tearability | ●●●● |

Evaluation across relevant tesa® assortment: very good ●●●● good ●●● medium ●● low ●

For the latest information on this product please visit <http://www.tesa.com/consumer>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

Additional Information & Pictures

Features

- Extremely strong hold
- Robust backing
- Extremely weather-resistant and waterproof
- UV resistant
- For indoor and outdoor use
- Can be used on rough surfaces
- Hand-tearable



For the latest information on this product please visit <http://www.tesa.com/consumer>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.