

Product Datasheet model uvex pheos 9192 415

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

1. Product Characteristics

- sporty, timeless safety spectacle, frameless design allowing for an extra-large field of vision
- ergonomically shaped side arms with soft-grip temple ends provide a comfortable, secure fit without pressure
- nose bridge designed for all-day comfort
- robust polycarbonate lens with uvex 's proven supravision coating technology – permanent antifog lens
- UV400 – 100 % protection against dangerous UVA and UVB radiation up to 400 nm
- optional clip-in frame seal provides extra protection against particles, dirt and dust
- headband option holds eyewear in place during overhead or work in confined spaces
- standard size
- fits the uvex IES system
- metal-free

2. Technical Details Body

Temple

Material	POM/TPE
Colour	anthracite, blue


Marking

Manufacturer 's ID code	W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperature	T
Conformity symbol	CE

3. Technical Details Lens





Material	PC
Thickness	2.1 mm at PD
Coating	uvex supravision ETC
Colour	clear
UV protection	UV400

Marking

Filter	2C-1,2 (EN 170)
Manufacturer 's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperature	T
Scratch resistance	K
Antifog	N
Conformity symbol	CE
Factory symbol	

4. Logistical Information

Product

Weight	29g		
Dimensions (L x W x B) in approx. mm			
	162 x 145 x 49		
	Packing unit 1	Packing unit 2	Packing unit 3
EAN Code	4031101922324	4031101922324	4031101922324
Quantity in pcs.	1	10	160
Dimensions (L x W x H) in approx. mm			
	55 x 150 x 60	185 x 290 x 97	600 x 400 x 400
Net weight in approx. g	29	290	4,640
Gross weight in approx. g	55	653	11,350
Country of Origin	Germany		

5. Miscellaneous

Standards	EN 166 + EN 170
PPE Category	Category II