



Vacuum Cleaner Mini (EU)

Clean up anywhere anytime



ID: 34180 SKU: BHR5156EU

6000 Pa suction power

- Brushless DC motor, rotating up to 63000 revolutions per minute;

Up to 30mins lasting time

- Running up to 30mins, no need to worry about charging;

One-click to empty dust bin

- Press down the button to empty the dustbin;
- Press up the button to lock the dustbin;

Lightweight & Portable

- Weighs only 500g, lighter than a bottle of water;
- Easy to carry around and store;

Washable filter

- Whole filtration rate over 99%;
- Simply wash the filter with water to clean, and restore when it's completely dry;

2 nozzle accessories

- Crevice nozzle
- Brush nozzle

* Replacement filter is sold separately

Mi Vacuum Cleaner Mini (EU)



Similar size, but lighter than a bottle of water



great suction power



2 different nozzles for more application



One-click to empty dust



Detachable and washable dustbin and filter

Mi Vacuum Cleaner Mini (EU)



Specification

Cordless	√
Electric motor	Brushless motor, max 63,000 revolutions/min
Suction power	6000 Pa
Duration	Up to 30mins
Nozzle	2
Filter	Washable filter and stainless steel filter
LED indicator	√
Dustbin capacity	50ml
One-click empty	√
Charging port	Type-C, adapter
Weight	500g
Size	267*55*50mm