

Shore Power Cable

www.victronenergy.com



Shore Power Cable

- CE certified
- Waterproof IP 56 shore power cable and inlet
- Moulded plug and connector
- Power indication LED
- Protection cap on female connector
- Stainless steel or Polyamide inlet
- Many different adapter cords available, see our pricelist for details



Shore Power Organiser Bag



Shore Power Inlet
stainless steel 3-pole



	SHP302501500	SHP302502500	SHP304001500	SHP304002500
Current Rating (A)	16A	16A	25A	25A
Voltage Rating (VAC)	250	250	250	250
Plug Type	Moulded IEC 60309 2p+E	Moulded IEC 60309 2p+E	Moulded IEC 60309 2p+E	Moulded IEC 60309 2p+E
Plug Colour	Blue	Blue	Blue	Blue
Connector Type	Moulded IEC 60309 3-Pole	Moulded IEC 60309 3-Pole	Moulded IEC 60309 3-Pole	Moulded IEC 60309 3-Pole
Connector Colour	Black / Yellow	Black / Yellow	Black / Yellow	Black / Yellow
LED light and protection cap on female connector	yes	yes	yes	yes
Cable Type	H07BQ-F 3x 2,50mm ²	H07BQ-F 3x 2,50mm ²	H07BQ-F 3x 4,00mm ²	H07BQ-F 3x 4,00mm ²
Cable Colour	Yellow	Yellow	Yellow	Yellow
Cable Length (m)	15	25	15	25
Cable Size (mm ²)	2,50	2,50	4,00	4,00
Weight (kg)	2,66	4,3	4	7
CE Certified	yes	yes	yes	yes

Accessories

Power Inlet	SHP301602000	SHP303202000	SHP301603000
Current Rating (A)	16	32	16
Voltage Rating	250	250	250
Standard	IEC 60309, 2p+E	IEC 60309, 2p+E	IEC 60309, 2p+E
Cover	Solid cast 316 Stainless Steel	Solid cast 316 Stainless Steel	Glass filled PA6
Plug body	PA6	PA6	PA6
Pins	Brass, Nickel plated	Brass, Nickel plated	Brass, Nickel plated
Weight (kg)	0,34	0,65	0,23
Waterproof	IP 56	IP 56	IP 56
CE Certified	yes	yes	yes



Adapter Cord



Adapter Cord



Splitter Cord



Adapter Cord



Adapter Cord