

# Solar Ground Lights

## User Manual

### Specification:

Solar Panel: 2V/0.3W Monocrystalline silicon  
Battery: 1.2V/800mAh NiMH AA battery  
Power Source: Solar power  
LED Source: 12 5050 0.2W warm lights  
Charging Time: 4-6 hours  
Working Time: 8-10 hours after fully charged  
Waterproof Class: IP67  
Color Temperature: 3000-3500K  
Material: ABS

### Package Instruction

1\*Lamp head  
2\*Ground plug in  
1\*User manual

### Product Features:

1. Light control mode, the lamp will light up at night and turn off at sunrise automatically.
2. Solar energy is automatically charged during the day, and it will be converted into electricity at night.
3. The lighting time is more than 10 hours with fully charged.
4. Place of use: garden lawn, walkway, courtyard, yard, park etc.

### Operation Instructions:

1. ON/OFF setting: press the ON/OFF button to turn on the power before use.
2. Installation method: insert into the ground directly.
3. Working environment: please install it in the place with direct sunlight.

### Note:

1. Although this product has waterproof function, do not soak it in water or put it in a place with water.
2. If not use the product for more than one week after receiving please put it under the sunlight for charging before use.
3. The switch on the solar panel should be turned on before charging or it won't be charged



12 Lamp beads

### Product Structure

