

KERN 347-045

KERN

Individual weight, OIML Class M1, 10 g, Slot weight (Type A), stainless steel fine turned



Dimensions packaging (W×D×H)	22×22×5 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-050-400
-------------------------------	-------------

Product information

GTIN/EAN number	4045761256286
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M1
Product family	347

Measuring System

Test weight - volume (cm ³)	1,1905
Test weight - Density uncertainty (kg/m ³)	100
Test weight - volume uncertainty (cm ³)	0,0241
Weight OIML class	M1
Test weight - nominal value	10 g
Permissible tolerance according to OIML (+/-)	2 mg
Test weight - Density (kg/m ³)	8000
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2600

Construction

Shape weight	Slot weight (Type A)
Dimensions (Ø×H)	22×5 mm
Material	stainless steel fine turned
Adjustment method	Polishing

Services (optional)

Article number for DAkkS calibration	962-634
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
---------------	-----