

KERN 347-055

KERN

Individual weight, OIML Class M1, 20 g, Slot weight (Type A), stainless steel fine turned



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M1
Product family	347

Measuring System

Test weight - volume (cm ³)	2,381
Test weight - Density uncertainty (kg/m ³)	100
Test weight - volume uncertainty (cm ³)	0,0482
Weight OIML class	M1
Test weight - nominal value	20 g
Permissible tolerance according to OIML (+/-)	2,5 mg
Test weight - Density (kg/m ³)	8000
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2600

Construction

Shape weight	Slot weight (Type A)
Dimensions (Ø×H)	27×6 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-635
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	27×27×6 mm

Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-080-400
-------------------------------	-------------

Product information

GTIN/EAN number	4045761256293
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

