

KERN 367-07

KERN

Individual weight, OIML Class M3, 100 g, Knob, stainless steel fine turned



Category	
Brand	KERN
Product category	Individual weight
Product group	OIML M3
Product family	367

Measuring System	
Test weight - volume (cm ³)	11,9048
Conformity assessment possible	no
Test weight - Density uncertainty (kg/m ³)	140
Test weight - volume uncertainty (cm ³)	0,2409
Weight OIML class	M3
Test weight - nominal value	100 g
Permissible tolerance according to OIML (+/-)	50 mg
Test weight - Density (kg/m ³)	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	1500

Construction	
Shape weight	Knob
Dimensions (Ø×H)	22×37 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)	
Article number for DAkkS calibration	962-637

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	22×22×37 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-070-400
Case - Aluminium article number	317-070-600
Case - Wood article number	337-070-200

Product information

GTIN/EAN number	4045761257269
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

