# SAUTER **CP 50-3P7**

Single-Point load cell made of stainless steel



## Category

| | |
|---|---|
| Brand | Sauter |
| Product categoriy | Measuring cell |
| Product group | Load cell |
| Product family | CP P7 |

## Measuring System

| | |
|---|---|
| Weighing capacity [Max] | 50 kg |
| Load cell - characteristic value - nominal | 2 mV/V |
| Load cell - characteristic value - variance | 0,2 mV/V |
| Load cell OIML class | C3 |
| Load cell connection | 6-wire |
| Power supply + Colour | red |
| Power supply - Colour | black |
| Signal + Colour | green |
| Signal - Colour | white |
| Sense + Colour | 75392 |
| Sense - Colour | 75402 |
| Load cell - Resolution (verifiable) | 3000 e |
| Load cell - Dead load [Min] (%) | 0% |
| Measuring applications | mass |
| Directions of force | compression |
| Load cell - Y-value | 12000 |
| Load sell - Input resistance - nominal | 384 Ω |
| Load cell - Input resistance - variance | 4 Ω |
| Load cell - Output resistance - nominal | 350 Ω |
| Load cell - Output resistance - variance | 3 Ω |
| Load cell - Recommended exitation voltage [Min] | 5 V |
| Load cell - Recommended exitation voltage [Max] | 12 V |
| Load cell - Isolation resistance - [Min] | 5000 MΩ |
| Load cell - Combined error | 0,023% |
| Temperature coefficient - characteristic value | ± 0.011% F.S. / 10 °C |
| Zero balance | ≤± 1.5%FS |
| Temperature coefficient - zero signal | ± 0.015% F.S. / 10 °C |
| Creep error (30 minutes) | ≤± 0.016%FS |
| Safe overload | 150% |
| Ultimate overload | 300% |

## Functions

| | |
|---|---|
| IP protection - complete device | IP67 |

## Construction

| | |
|---|---|
| Material | stainless steel |
| Design | Singlepoint load cell |
| Dimension (W×D×H) | 150×25,4×40 mm |
| Maximum platform size | 400×400 mm |
| Cable length | 1 m |
| Mounting - force application | 2 × threaded hole M6 |
| Mounting - force dissipation | 2 × threaded hole M6 |

## Environmental conditions

| | |
|---|---|
| Ambient temperature [Min] | -35 °C |
| Ambient temperature [Max] | 65 °C |
| Use temperature [Min] | -10 °C |
| Use temperature [Max] | 40 °C |
| Storage temperature [Min] | -40 °C |
| Storage temperature [Max] | 70 °C |

## Approval

| | |
|---|---|
| CE mark | ✓ |

## Product information

| | |
|---|---|
| GTIN/EAN number | 4045761254060 |
| REACH classification | no prohibited substances |

## Packing & Shipping

| | |
|---|---|
| Shipping method | Parcel service |
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 235×115×45 mm |
| Net weight approx. | 1,00 kg |
| Gross weight approx. | 1,2 kg |
| Shipping weight | 1,05 kg |

# SAUTER **CP 50-3P7**

Single-Point load cell made of stainless steel

## Pictograms

### STANDARD




### OPTION

