

KERN ACJ 300-4M

KERN

The bestseller in analytical balances, with high-quality single-cell weighing system, verification optional



Category

Brand	KERN
Product category	Laboratory balance
Product group	Analytical balance
Product family	ACJ

Measuring System

Automatic adjustment - Standard temperature deviation	2 °C
Weighing system	Single-Cell
Weighing capacity [Max]	320 g
Automatic adjustment - Standard time interval	4 h
Readability [d]	0,0001 g
Reproducibility	0,0002 g
typical reproducibility	0,00006 g
Linearity	± 0,0003 g
Minimum weight [Min]	0,01 g
Conformity assessment possible	✓
Resolution	3.200.000
Adjustment options	Internal calibration (automatic)
	Adjusting with internal weight (manual)
Recommended adjusting weight	300 g (E2)
Stabilization time	3 s
Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,0005 g
Units (if device is conformity assessed)	g mg ct
Minimum weight [Min] (ct)	0,1 ct

USP Minimum weight of sample (k = 2, U = 0.1%)	400 mg
typical USP Minimum weight of sample	120 mg
Construction type of the scale	Single-range balance
Units	g mg ct
Weighing capacity [Max] (ct)	1600 ct
Readability carat [d] (ct)	0,001 ct
Default unit	g

Display

Display type	LCD
Display type	LCD
Display backlight	no
Display screen size	115×32 mm
Display digit height	14 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	213×333×338 mm
Dimensions rectangular draught shield - inner (W×D×H)	174×162×227 mm
Dimensions rectangular draught shield - outer (W×D×H)	201×220×256 mm
Dimensions weighing surface (Ø)	91 mm
Dimensions weighing surface	91 mm
Material housing	cast aluminium, plastic
Material weighing plate	stainless steel
Material draught shield	glass
Material display housing	plastic
Level indicator	✓
Levelling feet adjustable	✓

Functions

Sum memory function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Density determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	320.000
Counting reference weight can be entered	✓

KERN ACJ 300-4M



The bestseller in analytical balances, with high-quality single-cell weighing system, verification optional

Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Reference quantity	5, 10, 20, 50, 100
Auto-off interval(s) in mains power mode	0 - 99 min
Tare function	manual (multi)
Number of keys for operation	6

Interface

Interfaces	RS-232 standard USB-Device
------------	-------------------------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter

Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
---	-------------------------------

Plug-in power supply / adapter for countries - optional	EURO UK US CH
---	------------------------

Input voltage power supply / power [Max]	110 V - 230 V AC
--	------------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	12 V, 1 A
------------------------------------	-----------

Power socket for mains adapter	Hollow plug, inside minus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
--------------------------------	---

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Humidity of environment [Min]	20 %
Humidity of environment [Max]	85 %
Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	I
Verification scale interval [e]	0,001 g

Verification scale interval [e] (ct)	0,01 ct
--------------------------------------	---------

Services (optional)

Article number for conformity assessment	965-201
Article number for DAkkS calibration	963-101
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	390×570×530 mm
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	9 kg
Shipping weight	23,6 kg

Product information

GTIN/EAN number	4045761235663
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



FACTORY

