

KERN OBL 156

KERN

High-quality phase contrast microscope – specially pre-configured with a series of options for flexible expansion



Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBL-15

Construction

Dimension (W×D×H)	394×185×377 mm
Optical system	Infinity
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Butterfly
Light distribution	20:80

Contrasting methods

Bright field
Darkfield (optional)
Phase contrast
Polarisation (optional)
Fluorescent (optinal)

Standard objectives

4×
100×
PH 10×
PH 40×

Lens quality	Infinity E-Plan / Plan
Nosepiece screw-in locations	4
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

Ocular

Ocular type	Eyepiece HWF 10x / Ø 20mm with anti-fungus, high eye point
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

Objective

Objectives - Details	PH-Objective Infinity Plan 10x / 0,25 anti-fungus Objective Infinity E-Plan 100x / 1,25 oil, spring, anti-fungus Objective Infinity E-Plan 4 x / 0,11 anti-fungus PH-Objective Infinity Plan 40x / 0,66 spring, anti-fungus
Objectives magnifications	4x / 10x / 40x / 100x

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Illumination dimmable	Transmitted light
Filter possible	✓
Phase-contrast unit	PH condenser for single slot
Field diaphragm	✓

Focussing

Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

Condensor

Condensor type	Phase contrast condenser
----------------	--------------------------

Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------

KERN OBL 156



High-quality phase contrast microscope – specially pre-configured with a series of options for flexible expansion

Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Power supply cable removable	removable
Input voltage device / power [Max]	5 V, 1 A

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	420×275×450 mm
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	10,4 kg

Product information

GTIN/EAN number	4045761267800
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

