

KERN OIV 656

The professional video microscope with auto-focus



Category

Brand	Optics
Product category	Microscopes
Product group	Stereo microscope

Technical data about verification

CE mark	✓
---------	---

Construction

Dimensions	372×285×482 mm
Contrast procedure	[Value missing]
Optical system	Axial
Resolution	2 MP
Type of sensor	CMOS
Sensor size	1/2,8"
Camera colour depth	Farbe
Camera frame rate	30 fps

Functions

Memory functionality	✓
Memory/database - total size	128 GB

Fokussierung

Zoom (min.)	0,7 x
Zoom (max.)	4,5 x
Field of view (Min)	2,65 mm
Field of view (Max)	12,64 mm
Magnification ratio	32207
Focussing mechanism	47952

Beleuchtung

Lighting direction	Reflecting
Dimmable lighting	Auflicht

Power supply

Power supply delivered with the product	Power supply unit
Type of power supply	Built-in power supply
Power supply / Adapter countries within the scope of delivery	EURO
Input voltage for device/max. power	100 - 240 V

Packing & Shipping

Dimensions of packaging	420×350×630 mm
Net weight approx.	7 kg
Gross weight approx.	15 kg
Total delivery time	1 d
Art des Versands	Parcel service

Pictograms

STANDARD

