

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2069940100](#)

Status: **Active**

Overview: [Internet of Things \(IoT\) Antennas: Wi-Fi, Bluetooth, Zigbee](#)

Description: Wi-Fi 6E Flex Cabled Side-Fed Antenna, 6.40mm Width, 15.40mm Cable Length, 100.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

Documents:

3D Model	Application Specification 2069940100-AS (PDF)
Drawing (PDF)	Packaging Specification 2069940100-PK (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2069940100-PS (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	Antennas
Series	206994
Component Type	Flexible Antenna with Cable
Function	Signal
Mates With	734120110 Microcoaxial RF, 50 Ohm
Overview	Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Product Name	2.4/5GHz Flexible Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Zigbee
Type	Wi-Fi Antenna
UPC	191128861236

Physical

Cable Length	100.00mm
Length	15.40mm
Mounting Style	Adhesive
Net Weight	0.571/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.15mm
Width	6.40mm

Electrical

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5850
Band#2 F_Start (MHz)	5150
Electrical Connectivity	Cable
Peak Gain (dBi)	3.6 @ 5 GHz
Return Loss - S11 (dB)	< -10, < -5
Total Efficiency	>55% @2.4 GHz, >70% @ 5 GHz

Material Info

Reference - Drawing Numbers

Application Specification	2069940100-AS
Packaging Specification	2069940100-PK
Product Specification	2069940100-PS
Sales Drawing	2069940100-SD

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[206994 Series](#)