




## TRILEDO Single

indoor surface-mounted ceiling light, QPAR51, white, max 10W

The rotating and swivelling ceiling light TRILEDO SQUARE CL is made of aluminium and comes in housing colours of white, brushed aluminium and matt black. Thanks to its aluminium lamp head, the cone of light can be individually aligned. Equipped with one GU10, the luminaire makes it possible to connect directly to a 230V mains voltage supply.



## TECHNICAL DATA

Item no.:	1002015
Socket	GU10
Lamp	LED GU10 51mm
Number of sockets	1
Lamps included	No
Primary nominal voltage	220-240V ~50/60Hz mA/V
Tilt range	20 °
Horizontal rotation range	350 °
Length	8.5 cm
Width	8.5 cm
Height	9.5 cm
Net weight	0.862 kg
Gross weight	0.962 kg
IP Code	IP 20
Safety class	I
Assembly	Surface
Assembly details	Ceiling
Wattage	10 W
Color	white
BIG WHITE Page	266

## Recommended lamp

1004973	LED QPAR51 , lightbulb GU10 300K 36°
1005075	LED lightbulb QPAR51 , GU10, 2700K, grey
1005080	LED lightbulb QPAR51 , GU10, 3000K, black
1005273	QPAR51 GU10 , LED light, 6W 2200 2700K CRI90 36°