


ASTINA QPAR51

Indoor pendant, white

The ASTINA high-voltage pendant is made from aluminium and is suitable for the use of GU10 halogen and for retrofitting LED lamps. The housing of the luminaire is equipped with a glass cover, which provides colour differentiation by means of indirect illumination. The ASTINA PD is supplied ready for direct connection to a 230V mains power supply.



TECHNICAL DATA

Item no.:	1002937
Socket	GU10
Lamp	QPAR51
Number of sockets	1
Lamps included	No
Primary nominal voltage	220-240V ~50/60Hz mA/V
Pendant length	250 cm
Height	20 cm
Diameter	7 cm
Net weight	0.652 kg
Gross weight	0.825 kg
IP Code	IP 20
Safety class	I
Assembly details	Ceiling with Acc.
Wattage	10 W
Color	white
BIG WHITE Page	160

Recommended lamp

1004972	LED QPAR51 , lightbulb GU10 2700K 36°
1005076	LED lightbulb QPAR51 , GU10, 2700K, white
1005082	LED lightbulb QPAR51 , GU10, 4000K, white
1005311	QPAR51 GU10 tunable smart , white / transparent LED light, 5W 2700-6500K CRI90 38°

Accessories

1001542	PENDANT ADAPTER , for 240V 3-circuit track, traffic white, incl. installa- tion accessories
1001818	FITU triple ceiling plate , long, black
1001819	FITU triple ceiling plate , long, white
132600	CEILING PLATE FITU , single ceiling plate, round, black, incl. strain-relief
132601	CEILING PLATE FITU , single ceiling plate, round, white, incl. strain-relief
132605	CEILING PLATE FITU , single ceiling plate, round, chrome, incl. strain-re- lief
132610	CEILING PLATE FITU , triple ceiling plate, round, black, incl. strain-relief
132611	CEILING PLATE FITU , triple ceiling plate, round, white, incl. strain-relief
132615	CEILING PLATE FITU , triple ceiling plate, round, chrome, incl. strain-relief
143120	PENDANT ADAPTER , for 1-phase high-voltage surface-mounted track, black, incl. strain relief and threaded piece

143121	PENDANT ADAPTER , for 1-phase high-voltage surface-mounted track, white, incl. strain relief and threaded piece
143124	PENDANT ADAPTER , for 1-phase high-voltage surface-mounted track, silver-grey, incl. strain re- lief and threaded piece
145990	PENDANT ADAPTER , for 240V 3-phase track, black, incl. installation ac- cessories
145994	PENDANT ADAPTER , for 240V 3-phase track, grey, incl. installation ac- cessories