




HELIA AMBIENT 35

indoor LED pendant black flat canopy

With the HELIA AMBIENT 35 you have a recessed pendant with a puristic and clear design. The luminaire is available in versions with and without a ceiling plate. A warm white premium LED is integrated which produces an especially pleasant light thanks to the acrylic insert. The luminaire is supplied with a connection lead / suspension.



TECHNICAL DATA

Item no.:	1003435
Secondary power / secondary voltage	500mA
Length	38 cm
Pendant length	200 cm
Diameter	3.5 cm
Installation diameter	6.8 cm
Installation depth	3 cm
Net weight	0.656 kg
Gross weight	0.95 kg
Safety class	III
Assembly	Recessed
Assembly details	Ceiling
Wattage	7.5 W
Lumen	425 lm
Colour temperature	3000 Kelvin
Color	black
CRI	90
LXXBXX data	L70B50
BIG WHITE Page	157

Light Source

916381	
--------	---

Accessories

464091	LED DRIVER , 9VA, 500- mA, incl. strain relief
464141	