




## HELIA AMBIENT 35

indoor LED pendant TRIAC black with canopy

The HELIA AMBIENT 35 is a pendant with a puristic and clear design. The luminaire is available in versions with and without a ceiling plate. A warm white premium LED is integrated which produces an especially pleasant light thanks to the acrylic insert. The luminaire is supplied with a connection lead / suspension.



## TECHNICAL DATA

Item no.:	1003436
Primary nominal voltage	220-240V ~50/60Hz mA/V
Secondary power / secondary voltage	500mA
Length	38 cm
Pendant length	200 cm
Diameter	3.5 cm
Net weight	0.972 kg
Gross weight	1.2 kg
Safety class	I
Assembly	Surface
Assembly details	Ceiling
Dimmable	Yes
Dimming technology	trailing edge
Wattage	9 W
Lumen	425 lm
Colour temperature	3000 Kelvin
Color	black
CRI	90
LXXBXX data	L70B50
Minimum ambient temperature	-20 °C
Maximum ambient temperature	30 °C
BIG WHITE Page	157

## Light Source

916381

