




## FITU

pendant, A60, round, black, 5m cable with open cable end, max. 60W

The FITU pendant suspension with open cable end is from our MIX & MATCH pendant system and is available in various colours. The FITU product family impresses with its wide variety of application possibilities. Thanks to the fitted E27 socket, the luminaire is suitable for LED and energy-saving lamps. The electrical connection is made directly to the 230V mains supply.



## TECHNICAL DATA

Item no.:	132690
Socket	E27
Number of sockets	1
Primary nominal voltage	220-240V ~50/60Hz mA/V
Pendant length	500 cm
Height	9.1 cm
Diameter	4.4 cm
Net weight	0.333 kg
Gross weight	0.381 kg
IP Code	IP 20
Safety class	II
Assembly	Surface
Assembly details	Ceiling with Acc.
Wattage	60 W
Color	black
Maximum ambient temperature	30 °C
BIG WHITE Page	150

## Recommended lamp

1005303	A60 E27 , transparent LED light, 7.5W 2700K CRI90 320°
1005304	A60 E27 , Frosted LED light, 7.5W 2700K CRI90 320°