



## GLENOS

profile pendant light, LED, 4000K, black, 2 m, 85W

The GLENOS pendant light is equipped with a high-output LED strip, offering you top-class, powerful LED lighting. These pendant lights are available in various lengths and colours and come with a 2.5 m power cable, which can be individually shortened. Thanks to the dimmable LED driver, the GLENOS pendant light is ready to connect to the 230 V mains power supply.

### TECHNICAL DATA

Item no.:	1001409
Number of different light outlets	1
Primary nominal voltage	220-240V ~50/60Hz mA/V
Secondary power / secondary voltage	1000mA
Length	205 cm
Pendant length	200 cm
Width	5 cm
Height	7 cm
Net weight	4.491 kg
Gross weight	5.353 kg
IP Code	IP 20
Safety class	I
Assembly	Surface
Assembly details	Ceiling
Dimmable	Yes
Dimming technology	1-10V
Wattage	85 W
Lumen	6600 lm
Colour temperature	4000 Kelvin
Color	black
CRI	80
UGR ≤	28

## Light Source

916328	
--------	---

## Accessories

470505	EP1 DIMMER, 1-10V, max. 10W
--------	--------------------------------

LXXBXX data	L70B50
Minimum ambient temperature	-20 °C
Maximum ambient temperature	50 °C
BIG WHITE Page	143