




## FITU PD

indoor pendant, E27, soft gold, max. 60W, 5m

The FITU pendant with an open cable end can be combined with any colour variant of our FITU ceiling canopies. With its built-in E27 socket, the luminaire is suitable for both LED and energy-saving lamps. Pendant length is 500 cm and can be shortened depending on installation needs. Supplied ready for direct connection to 230V mains supply.



## TECHNICAL DATA

Item no.:	1002168
Socket	E27
Number of sockets	1
Primary nominal voltage	220-240V ~50/60Hz mA/V
Pendant length	500 cm
Height	9.1 cm
Diameter	4.4 cm
Net weight	0.34 kg
Gross weight	0.388 kg
IP Code	IP 20
Safety class	II
Assembly	Surface
Assembly details	Ceiling with Acc.
Wattage	60 W
Color	gold
Maximum ambient temperature	30 °C
BIG WHITE Page	150

## Recommended lamp

1005303	A60 E27 , transparent LED light, 7.5W 2700K CRI90 320°
---------	--