




FITU PD E27

indoor pendant, white, 5m cable with open cable end

The narrow version of the FITU pendant with open cable ends can be combined with FITU ceiling canopies in any colour variant. With its built-in E27 socket, the luminaire is suitable for both LED and energy-saving lamps. Pendant length is 500 cm and can be shortened depending on installation needs. Supplied ready for direct connection to 230V mains supply.



TECHNICAL DATA

Item no.:	1002562
Socket	E27
Number of sockets	1
Primary nominal voltage	220-240V ~50/60Hz mA/V
Pendant length	500 cm
Height	40 cm
Diameter	4.4 cm
Net weight	0.667 kg
Gross weight	0.884 kg
IP Code	IP 20
Safety class	II
Assembly	Surface
Assembly details	Ceiling with Acc.
Wattage	60 W
Color	white
Maximum ambient temperature	30 °C
BIG WHITE Page	150

Recommended lamp

1005265	ST64 E27 , gold LED light, 7.5W 2500K CRI90 320°
1005303	A60 E27 , transparent LED light, 7.5W 2700K CRI90 320°
1005304	A60 E27 , Frosted LED light, 7.5W 2700K CRI90 320°
1005318	A60 E27 RGBW smart , white / milky LED light, 9W CRI90 230°