



## LED POWER SUPPLY 100W 24V TRIAC DIMMABLE

TRIAC dimmable LED power supply with maximum output of 100 W with a voltage of 24 V.

### TECHNICAL DATA

Item no.:	1003105
Primary nominal voltage	220-240V ~50/60Hz ma/V
Secondary power / secondary voltage	24V DC
Length	21 cm
Width	6.7 cm
Height	3.4 cm
Net weight	0.414 kg
Gross weight	0.436 kg
IP Code	IP 20
Safety class	II
Assembly	Surface
Dimmable	Yes
Dimming technology	trailing edge
Color	white
Minimum ambient temperature	-20 °C
Maximum ambient temperature	50 °C
BIG WHITE Page	796