




## ASTINA QPAR51

### Indoor surface-mounted ceiling light, white

The ASTINA high-voltage ceiling light is made from aluminium and is suitable for the use of GU10 halogen as well as for retrofitting LED lamps. The housing of the luminaire is equipped with a glass cover, which provides colour differentiation by means of indirect illumination. The ASTINA CL is supplied ready for direct connection to a 230V mains power supply.



### TECHNICAL DATA

Item no.:	1002934
Socket	GU10
Lamp	QPAR51
Number of sockets	1
Lamps included	No
Primary nominal voltage	220-240V ~50/60Hz mA/V
Height	14.5 cm
Diameter	7 cm
Net weight	0.418 kg
Gross weight	0.514 kg
IP Code	IP 20
Safety class	I
Assembly	Surface
Assembly details	Ceiling
Wattage	10 W
Color	white
BIG WHITE Page	287

## Recommended lamp

1004972	LED QPAR51 , lightbulb GU10 2700K 36°
1005075	LED lightbulb QPAR51 , GU10, 2700K, grey
1005079	LED lightbulb QPAR51 , GU10, 3000K, white
1005082	LED lightbulb QPAR51 , GU10, 4000K, white