


FENDA

floor stand, lamp base, TC-(D,H,T,Q)SE, brushed metal, without shade, max. 60W

We offer a new basic design for living room lights with the FENDA floor stand. The brushed metal base allows it to be combined with various shades from the FENDA series. Prepared to take LED or energy-saving lamps with an E27 socket, the FENDA is ready for direct connection to the 230V mains supply. In addition, a switch is included located in the connection lead.



TECHNICAL DATA

Item no.:	155795
Socket	E27
Number of sockets	1
Primary nominal voltage	220-240V ~50/60Hz mA/V
Height	145 cm
Diameter	28 cm
Net weight	5.657 kg
Gross weight	6.479 kg
IP Code	IP 20
Safety class	II
Impact resistance class	IK03
Impact resistance	0,35 Joule
Assembly	Mobile
Wattage	60 W
Color	nickel
Maximum ambient temperature	40 °C
BIG WHITE Page	104

Recommended lamp

1005301	A60 E27 , white LED light, 9W 2700K CRI90 220°
1005303	A60 E27 , transparent LED light, 7.5W 2700K CRI90 320°
1005304	A60 E27 , Frosted LED light, 7.5W 2700K CRI90 320°
1005318	A60 E27 RGBW smart , white / milky LED light, 9W CRI90 230°