





客户料号:2521352

产品图号:

版次	说明	变更日期	变更者
A/0			



技术要求: requirement:

- 1: 耐压测试: 外高压4200V/S; 内高压1500V/S; 0.5MA
Dielectric voltage :between jacket and conductors 4200V/S
between conductors 1500V/S
- 2: 绝缘阻抗不小于100兆欧.
Insulation resistance 100MΩ.
- 3: 100%导通OK.
Continuity of lead 100% OK.
- 4: 符合ROHS.
RoHS COMPLIANT.

5	纸扎带	2	EA
4	XR-1638137 线上条形码标签 白底黑字	1	EA
3	品字尾插座IEC C13 (XR-501), COLOR: 黑色Black, PVC	1	EA
2	品字公插座IEC C14 (XR-602), COLOR: 黑色Black, PVC	1	EA
1	H05VV-F 3G0.75mm², COLOR: 黑色Black	1	EA
NO.	DESCRIPTION	QTY	UNIT

DESCRIPTION	DRAW NO.	XR-1638137	UNIT	M M
PARTS NO	SCALE	NONE	DATE	23/01/2022
APPROVED	CHECKED		DRAWING	梁静雅