






客户料号:2521358

产品图号:

版次	详细描述	变更日期	变更者
A/0			



线材印字为凹印, 字轮编号: SY08; wire marking:
 SAA-182409-EA 4V-75 H05VV-F 3X1.0mm² 250/440V ORDINARY



技术要求: requirement:
 1: 耐压测试: 外高压4200V/S; 内高压2500V/S; 0.5MA
 Dielectric voltage :between jacket and conductors 4200V/S
 between conductors 2500V/S
 2: 绝缘阻抗不小于100兆欧.
 Insulation resistance 100MΩ.
 3: 100%导通OK.
 Continuity of lead 100% OK.
 4: 符合ROHS.
 RoHS COMPLIANT.

5	纸扎带	2	EA
4	XR-1638130线上条形码标签 白底黑字	1	EA
3	品字尾插座C13(XR-501) COLOR: 黑色Black, PVC	1	EA
2	澳洲公三插(XR-351A) COLOR: 黑色Black, PVC	1	EA
1	H05VV-F 3X1.0mm ² , COLOR: 黑色Black	1	EA
NO.	DESCRIPTION	QTY	unit

DESCRIPTION		DRAW NO.	XR-1638130	UNIT	M M
PARTS NO		SCALE	NONE	DATE	11/01/2022
APPROVED		CHECKED		DRAWING	梁静雅