

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [2042230004](#)  
**Status:** **Active**  
**Overview:** [Squba Sealed Wire-to-Wire Connectors](#)  
**Description:** [Squba Sealed Plug Assembly, 1.80mm Pitch, 4 Circuits, Single Row, No Seal Plugs](#)

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[3D Model \(PDF\)](#)  
[Product Specification 2042200000-PS-000 \(PDF\)](#)  
[Product Specification 2042200000-TS-000 \(PDF\)](#)  
[Application Specification 2042200000-AS-000 \(PDF\)](#)  
[Packaging Specification 2042230000-PK-000 \(PDF\)](#)  
[Datasheet \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**  
UL E29179

**General**  
Product Family Crimp Housings  
Series [204223](#)  
Application Power, Signal, Wire-to-Wire  
Overview [Squba Sealed Wire-to-Wire Connectors](#)  
Product Name Squba  
UPC 191128320320

**Physical**  
Circuits (maximum) 4  
Circuits Detail No Seal Plugs  
Color - Resin Black  
Flammability 94V-0  
Gender Plug  
Glow-Wire Capable No  
Keying to Mating Part None  
Lock to Mating Part Yes  
Material - Resin Nylon  
Net Weight 2.760/g  
Number of Rows 1  
Packaging Type Bag  
Panel Mount No  
Pitch - Mating Interface 1.80mm  
Pitch - Termination Interface 1.80mm  
Polarized to Mating Part Yes  
Temperature Range - Operating -40° to +105°C

**Material Info**

**Reference - Drawing Numbers**  
Application Specification 2042200000-AS-000  
Packaging Specification 2042230000-PK-000  
Product Specification 2042200000-PS-000, 2042200000-TS-000  
Sales Drawing 2042230000-SD-000



Series image - Reference only

**EU ELV**  
**Not Relevant**

| <b>EU RoHS</b>                                                | <b>China RoHS</b> |
|---------------------------------------------------------------|-------------------|
| <b>Compliant</b>                                              |                   |
| <b>REACH SVHC</b>                                             |                   |
| Not Contained Per -<br>D(2020)9139-DC (19<br>Jan 2021)        |                   |
| <b>Halogen-Free</b>                                           |                   |
| <b>Status</b>                                                 |                   |
| <b>Low-Halogen</b>                                            |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Green Image       |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Contained     |

**Search Parts in this Series**  
[204223](#) Series

**Mates With**  
Squba Sealed Receptacle Assembly [204220](#)  
<br>Squba Sealed Receptacle Cable  
Assembly [45145](#)

**Use With**  
Squba Male Terminal [2042261001](#)