

avidsen

2 YEARS
WARRANTY



HomeGate

WIFI RECEIVER MODULE

Open your gate and garage door remotely


Ref.127041



CONTROL YOUR GATE OR GARAGE DOOR FROM ANYWHERE.

This Wi-Fi receiver allows you to open and close most gates or garage doors from your smartphone or tablet while maintaining compatibility with the original remote controls. It is also compatible with Google Home and Alexa voice assistants "Activate the gate". The app reports the position of your gate so you can know whether it is open or closed.





Compatible with all garage door and gate motor drives on the market.



Environmentally-friendly
Avidsen Home strives to design environmentally friendly products for the entire life of the product.



PRODUCT BENEFITS

- Turn your phone into a remote control for your gate or your garage door.
- Compatible with all gate and garage door motor drives.
- Real-time information on the position of the gate (open, closed), notification from the application.
- Combine other Avidsen Home products with your gate or garage door, for example you can programme the HomeLight bulb to turn on when the gate opens.
- Your gate listens to your voice with Alexa and Google Home; once you link your Avidsen Home application with Amazon or Google, you can control your gate or garage door through voice commands: "Activate the gate", "Activate the garage door"

Works with the app



avidsen Home



Works with voice assistants




KIT CONTENTS

- 1 Wi-Fi module
- 1 position sensor with a 5 m cable
- 1 installation kit




TECHNICAL CHARACTERISTICS



Max. power	200W
Features	Opens gates and garage doors
Connection	Wired 1 output
Cable cross-section	Up to 1.5 mm ²
Use	Indoors and outdoors
Operating T°	-10°C/+50°C
Storage T°	-20°C/+70°C
Power supply	230 Vac/50 Hz
Average consumption	< 1 W
Position sensor	5 m cable Maximum distance between sensors: 10 mm
Installation	Close to gate or garage door
Colour	White
Protection rating	IP20



Radio protocol	WiFi
Radio frequency	2.4 GHz
Protocol	802.11 b/g/n
Radio range	- Unobstructed range: 50m - Masonry: 25m, through 3 walls max. - Reinforced concrete: 10 m, through 1 wall/floor max. - Plasterboard/Wood: 30 m, through 5 walls max.



Need some help?

Aidssy

will answer your questions on
www.avidsen.com



3345111270414