

# KERN 318-37



E2, 100 mg, Milligram weights, wire shape, stainless steel



## Category

Brand	KERN
Product category	Individual weights
Product group	OIML E2

## Measuring system

Tolerance (OIML)	0,016 mg
Nominal value	100 mg
OIML class	E2
Volume uncertainty (cm <sup>3</sup> )	0,0003
volume (cm <sup>3</sup> )	0,0125
Verification possible	✓

## Construction

Material	Stainless Steelpolished
Shape	Wire
Dimensions (block)	9×9×3 mm

## Packing & Shipping

Dimensions of packaging	9×9×3 mm
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Total delivery time	1 d
Art des Versands	Parcel service
Shipping weight	0,1 kg

## Dienstleistungen (optional)

DAkS/DKD - items	962-357
Verification items	952-357
Plus tolerance	921-357

## Pictograms

### STANDARD

