

# KERN 366-87



M3, 10 kg, rectangular weight, lacquered cast iron, maximum possible quantity per pallet: 60, flat rate (max. 300 kg): max. 30



## Pictograms

### STANDARD



#### Category

|                  |                    |
|------------------|--------------------|
| Brand            | KERN               |
| Product category | Individual weights |
| Product group    | OIML M3            |

#### Measuring system

|                                       |           |
|---------------------------------------|-----------|
| Tolerance (OIML)                      | 5 g       |
| Nominal value                         | 10 kg     |
| OMIL class                            | M3        |
| Volume uncertainty (cm <sup>3</sup> ) | 119,024   |
| volume (cm <sup>3</sup> )             | 1408,4507 |

#### Construction

|                    |                     |
|--------------------|---------------------|
| Material           | Cast iron lacquered |
| Shape              | Block               |
| Dimensions (block) | 190×95×109 mm       |

#### Packing & Shipping

|                         |                |
|-------------------------|----------------|
| Dimensions of packaging | 190×95×109 mm  |
| Net weight approx.      | 10 kg          |
| Gross weight approx.    | 10 kg          |
| Total delivery time     | 1 d            |
| Art des Versands        | Parcel service |
| Shipping weight         | 10 kg          |
| Items per pallet        | 60             |

#### Dienstleistungen (optional)

|                   |         |
|-------------------|---------|
| DAkKS/DKD - items | 962-644 |
|-------------------|---------|