

medisana®

Massage Gun Pro MG 500

Art.-No. 88985 | EAN 40 15588 88985 1

- Deep tissue massage for muscle activation and promotion of muscle regeneration
- For self-massage at different body areas, such as shoulder muscles, pectoral muscles, dorsal muscles, gluteus muscles, thigh muscles, calf muscles
- 3 powerful vibration level for deep muscle stimulation

- 4 massage head attachments in different shapes for multiple massage effects



High performance for powerful deep tissue massage



Application | Features

- Deep tissue massage for muscle activation and promotion of muscle regeneration
- For self-massage at different body areas, such as shoulder muscles, pectoral muscles, dorsal muscles, gluteus muscles, thigh muscles, calf muscles
- Helps soothing muscle fatigue and soreness, stimulates blood circulation and reduces muscle recovery time
- 3 powerful vibration level for deep muscle stimulation
- Light weight and ergonomic shape for easy control and comfortable use
- Small travel case for easy and convenient storage - perfect for use at home, while traveling or during exercise
- Long battery life (approx. 1.5 hours in working mode)
- Auto-Stop after 10 minutes

- 4 massage head attachments in different shapes for multiple massage effects:
 - Round:** For use on large muscle groups to activate muscles and promote blood circulation
 - Bullet:** For targeting specific areas such as trigger points or smaller muscle groups
 - Spinal:** For relaxing muscles around the spine
 - Pebble:** For the treatment of joint areas, deep tissue, fascia and trigger point areas

Technical Data

- Size: approx. 23.5 x 6 x 19 cm (incl. attachment)
- Weight: approx. 692 g (excl. attachment)
- Power supply: 100-240 V, 50-60 Hz, DC 9V 1A
- Battery: Lithium-Ion-battery (7.4 V 2.600 mAh)
- Charging time: approx. 2-3 h
- Vibration level:
 - Low (2,800 rpm)
 - Medium (3,400 rpm)
 - High (3,900 rpm)

Scope of Delivery

Massage Gun Pro, 4 massage head attachments, Adaptor, Manual, Travel case

Logistical Data

Sales packaging

1 pc | 34 x 23.5 x 8.6 cm | approx. 1.3 kg

Packaging unit

4 pcs | 37.6 x 36.5 x 26.5cm | approx. 7.3 kg