



WIRING DIAGRAM



MATERIAL LIST

③	OVER MOLD	PVC (Color: GREY RAL7035)	2	
②	CONNECTOR	RJ45 8P8C Shielded Plug, Pin Gold Plated 3u", Shell Nickel plating Transparence blue	2	
①	CABLE	S/FTP CAT. 6A (AWG27 BC+AL-FOIL)*4PAIRS +BRAID JACKET:LSZH OD:5.8±0.2mm GREY RAL7035	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
		NEW	2023-02-15	A
BY	CHK	REVISION RECORD MODIFICATION	DATE	REV.

NOTE:

- 100% OPEN SHORT, MISS WIRE TEST
- Fluke test :
TEST LIMIT:ISO 11801 Channel Class Ea
- PRINTING::CAT6A S/FTP 4x2x27AWG/7 LSZH ISO11801 & EN50173 & ANSI/TIA568C.2
- ROHS2.0 AND REACH COMPLIANT
- Working temperature:-10°C ~ + 60°C
Storage temperature:-20°C~+75°C
- Packing:paper ring

Renkforce					
CUSTOMER	CN	BN.	2523747		
PRODUCT NAME	CAT. 6A S/FTP 27AWG		UNIT	MM	
	DRAWN BY	CHECK BY	APPO BY	DATE	
	HASIA	ARVIN		2023-02-15	