

NEO MPS 3222



Sample image

Order symbol: NEO MPS 3222

Product nbr: 4850060

Description: Metal mounting plate

Remarks:

Including: Metal mountingplate

EAN: 6418074314765

EI. number:

- Finland: 3424421
- Denmark: 8212098129
- Sweden: 2506225

Dimensions:	Height	Width	Depth
-------------	--------	-------	-------

mm:	280	180	1.5
-----	-----	-----	-----

inch:	11.02	7.09	0.04
-------	-------	------	------

Materials:

Material: Stainless steel

Base colour:

Cover colour:

Gasket material:

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Certificates: