

NEO MPI 3222

FIBOX

Enclosing innovations



Sample image

Order symbol: NEO MPI 3222

Product nbr: 4850070

Description: Multiperforated plastic mounting plate

Remarks:

Including: Plastic mountingplate

EAN: 6418074314796

EI. number:

- Finland: 3424424
- Denmark: 8212098158
- Sweden: 2506228

Dimensions:	Height	Width	Depth
-------------	--------	-------	-------

mm:	280	180	3
-----	-----	-----	---

inch:	11.02	7.09	0.12
-------	-------	------	------

Materials:

Material: ABS

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Certificates: