

PW 343009 T



Sample image

Order symbol: PW 343009 T

Product nbr: 4901824

Description: PW Inspection
Protection window.

Remarks: DB3 lock. Transparent
cover

Including:

EAN: 6418074309747

EI. number:

- Finland:
- Denmark:
- Sweden:

Dimensions:	Length	Width	Height
-------------	--------	-------	--------

mm:		295	342
-----	--	-----	-----

inch:		10	12
-------	--	----	----

Materials:

Material: Polycarbonate

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term): -40 ... 120 °C

Temperature °C (continuous): -40 ... 80 °C

Temperature °F (short term): -40 ... 250 °F

Temperature °F (continuous): -40 ... 175 °F

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 94 V0

Glow Wire Test (IEC 695-2-1) °C: 960 °C

NEMA Class

Certificates: