

PW 454009 T



Sample image

Order symbol: PW 454009 T

Product nbr: 4901804

Description: PW Inspection Protection window.

Remarks: DB3 lock. Transparent cover

Including:

EAN: 6418074309730

El. number:

- Finland:
- Denmark:
- Sweden:

Dimensions:	Height	Width	Depth
-------------	--------	-------	-------

mm:	452	400	88
-----	-----	-----	----

inch:	16	14	
-------	----	----	--

Materials:

Material: Polycarbonate

Base colour:

Cover colour:

Gasket material:

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 94 V0

Glow Wire Test (IEC 695-2-1) °C: 960 °CC

NEMA Class

Temperatures:

Temperature °C (short term): -40 ... 120 °C

Temperature °C (continuous): -40 ... 80 °C

Temperature °F (short term): -40 ... 250 °F

Temperature °F (continuous): -40 ... 175 °F

Certificates: