

Data Sheet

SPECIFICATION FOR APPROVAL

2/3

Name:	EMI FILTER	Part No.:	RD1811043
YBX MODEL:	YB11P5-3A-S(R)	Customer P/N :	

3. CHARACTERISTICS:

(1) VOLTAGE RATING.....115/250VAC

(2) CURRENT RATING:

A. @ 115VAC.....3A RMS Max.

B. @ 250VAC.....3A RMS Max.

(3) OPERATING FREQUENCY: 50/60Hz

(4) LEAKAGE CURRENT: EACH LINE TO GROUND

A. @ 115VAC/60Hz.....0.3mA Max.

B. @ 250VAC/50Hz.....0.6mA Max.

(5) HIPOT RATING(FOR ONE MINUTE)


A. LINE TO GROUND.....2250VDC

B. LINE TO LINE.....500VDC

(6) IR: 50M ohm AT 500VDC ANY INPUT OR OUTPUT TO GROUND

(7) TEMPERATURE RANGE: -25°C~+85°C



4. ELECTRICAL SCHEMATIC:



L:2x2.5mH
Cx:0.15uF(X2)
Cy:2200pF(Y2)
R:1M ohm

5. SAFETY COMPLIANCE:

TUV : B0899310001

Drawing by	Checked by	Approved by	Ordering No.	Unit	Rev.
			YB11P5-3A-S(R)	mm	
					2018-11-26

Data Sheet


SPECIFICATION FOR APPROVAL

1/3

Name:	EMI FILTER	Part No.:	RD1811043
YBX MODEL:	YB11P5-3A-S(R)	Customer P/N :	

1. PART NUMBER: YB11P5-3A-S(R)

2. PHYSICAL DIMENSIONS:



0 ~ 10	±0.3
10 ~ 100	±0.5
100 ~ 150	±0.8
150 ~ 200	±1.0


Drawing by	Checked by	Approved by	Ordering No.	Unit	Rev.	Dimension Limit	Tolerance
			YB11P5-3A-S(R)	mm			
2018-11-26							


Data Sheet

SPECIFICATION FOR APPROVAL

Name:	EMI FILTER	Part No.:	RD1811043
YBX MODEL:	YB11P5-3A-S(R)	Customer P/N :	

6.Label:



Drawing by	Checked by	Approved by	Ordering No.	Unit	Rev.
			YB11P5-3A-S(R)	mm	
					2018-11-26