

CAB P 403017

FIBOX
Enclosing innovations



Sample image

Order symbol: CAB P 403017

Product nbr: 8104304

Description: Polyester cabinet


Remarks: Opaque door

EAN: 6418074050014

El. number:

- Finland: 3424135
- Denmark: 8212018015
- Sweden: 2539819

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key, screws for mounting plate/DIN-rail and wall fastening lugs with screws. Wall mounting screws not supplied.



Dimensions:	Height	Width	Depth
mm:	400	300	170
inch:	15.75	11.81	6.69

Materials:

Material:	Polyester
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term)::	-50 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-60 ... 285
Temperature °F (continuous):	-40 ... 175

Accessories:

FP 4030-D	Swing door/Front plate. for enclosures: (400 x 300 x 1)
MB CAB	Swing door kit
MP 4030	Mounting plate. for enclosures: (400 x 300 x 2)
MPX 4030	Back panel. for enclosures: (400 x 300 x 1)
FP 4030-2x12	Front Plate with DIN openings. for enclosures: (400 x 300 x 1)
MPP 4030	Back panel. for enclosures: (400 x 300 x 1)
MF 4030	Mounting Frame with DIN-rails. for enclosures: (400 x 300 x 1)

Rating:

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	0
UV resistance:	UL 508
Flammability Rating:	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	

Certificates: