

# Crimping pliers - CRIMPFOX DUO 16S - 1202877

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, contact type: insulated and uninsulated ferrules, standards/regulations: DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F, cross-section, minimum: 0.14 mm<sup>2</sup>, cross-section, maximum: 16 mm<sup>2</sup>, for TWIN ferrules up to 2 mm<sup>2</sup> x 6 mm<sup>2</sup>, automatic cross-section adjustment, rotating dies, lateral and front entry, crimping: square

## Your advantages

- Crimping at difficult-to-access points, thanks to rotating die
- Comfortable to use, thanks to low grip span with optimum manual force progression
- Suitable for TWIN ferrules, thanks to continuous automatic adjustment
- Process reliability, thanks to pressure lock and self-adjusting die



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 267674
GTIN	4063151267674
Weight per Piece (excluding packing)	386.800 g
Weight per piece (including packing)	386.800 g
Custom tariff number	82032000
Country of origin	Sweden
Sales Key	N2 - Print Acces.+ManTool
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Length (b)	180 mm
Width (a)	65 mm
Height (c)	25 mm

### General

Note	DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F
Color	black/green
Compression	Square crimp

# Crimping pliers - CRIMPFOX DUO 16S - 1202877

## Technical data

### General

Type of contact	Insulated and uninsulated ferrules
Material	Steel with plastic handle
Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	16 mm <sup>2</sup>
AWG min	26
AWG max	6
Die station	Crimping position 1
Cross section range, metric	16 mm <sup>2</sup> ... 0.14 mm <sup>2</sup>
Cross section range AWG	26 ... 6

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 11.0	21043811
eCl@ss 9.0	21043811

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

## Accessories

### Accessories

### Mounting material

## Crimping pliers - CRIMPFOX DUO 16S - 1202877

### Accessories

Replacement spring - CRIMPFOX/ SPR-4 - 1200288



Spare recuperating spring