

LogiLink®



Smoke Detector

With Non-Replaceable Battery

Art. No.: SC0016



Complies with
EN 14604
Standard

VdS
G 221022
Certificate



Built-in 10 Years
DC 3 V lithium battery



Great for Home/
Caravan Safety

Make Your Life Safer

This smoke detector built-in 10 years lithium battery has photoelectric sensor which is optimized to detect even slow smoldering fires. Alarm also features a loud 85 dB alarm, easy mounting bracket, a single test/silence button, and an end-of-life signal so you know when to replace the device. For maximum protection and the ultimate in assurance, you can depend on Logilink's Smoke Detector to secure what matters most in life.



85dB Alarm



Silent Mode



LED Indicator



Low Battery Warning



Easy to Install



SC0016



Made in China



Great for Home Safety



Great for Caravan Fire Safety

Highly Accurate & Responsive

Features photoelectric technology; the smoke detector responds to hazardous smoke quicker than traditional detectors. With an 85 dB alarm and a rapid flashing indicator, the alarm ensures complete protection by giving you enough time to control the fire or safely escape.

Self-Test & Silent Function

Built-in 3V lithium battery, which could keep for 10 years without replacing to protect environment. Comes with silent mode that allows you to avoid false alarms from cooking or steamy showers. Once pushed, silent mode is activated for only 10 minutes, then returns to normal functionality, thus keeping you and your family safe.

Guaranteed Quality

This smoke detector complies with the EN 14604 standard and with VdS approval G 221022, ensuring high quality and durability for home safety.

Protects Your Family

Place the smoke detector in anywhere you want to enhance the safety of your family; watches over you around the clock.



*The specifications and pictures are subject to change without prior notice.

*All trade names referenced are the registered trademarks of their respective owners.



SC0016



Made in China

LED Indicators:

States	LED Indication
Normal	Blinking red once every 40 seconds
Test/Alarm	The red LED will blink once per second; it will continue until the air is cleared or the test button is pushed
Silent Mode	The red LED will flash once every 8 seconds after pressing the test/silence button, the device is muted for 10 mins.
Low battery	Blinking red once every 40 seconds, short and quick beeps
Malfunction	16 seconds after the alarm chirping every 40 seconds, the red light flashes once

Specifications:

Power	Built-in DC 3 V Lithium Battery, not replaceable
Sensor Type	Photoelectric
Standby Current	<6 μ A
Alarm Current	<100 mA
Alarm Volume	>85 dB(A) at 3 meters
Alarm Sensitivity	0,100–0,160 dB/m
Operating Temperature	0–40 °C
Operating Humidity	<93 % RH (no condensation)
Storage Temperature	5–28 °C
Storage Humidity	30–70 %
LED Indicator	Yes
Silent Mode Time	Approx. 10 minutes
Mounting Methods	On wall or ceiling
Dimensions	Ø10x3,36 cm
Weight	91 g

Package Contents:

- » 1x Smoke Detector
- » 1x Mounting Kit
- » 1x User Manual

Package Information:

- » Packing Dimension: 104x104x50 mm
- » Packing Weight: 0,14 kg
- » Carton Dimension: 460x280x385 mm
- » Carton Q'ty: 60 pcs
- » Carton Weight: 9,2 kg



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



Made in China