

Model number: VC-12668685

Type designation: VRLA

Chemical system: AGM Technology

Number of cells: 6

Internal resistance: Fully Charged battery 77 °F (25 °C) 18 mOhms

Self-discharge: 3 % of capacity declined per month at 20 °C (average)

Short circuit current: 450 A

Energy content: 108 Wh

Nominal Voltage: 12 V

Nominal Capacity: 9 Ah

20 hour rate (0.45 A, 10.5 V)

Average weight: 2.8 kg

Dimensions: 151\*65\*94\*100 (mm)

Operating temperature:

Discharge -20~60 °C

Charge -10~60 °C

Storage -20~60 °C

Recommended storage temperature:

0 °C ~ 25 °C , no more than 6 months



