

Model number: VC-12713935

Type designation: VRLA

Chemical system: AGM Technology

Number of cells: 3

Internal resistance: Fully Charged battery 77 °F (25 °C) 30 mOhms

Self-discharge: 3 % of capacity declined per month at 20 °C (average)

Short circuit current: 160 A

Energy content: 19.2 Wh

Nominal Voltage: 6 V

Nominal Capacity: 3.2 Ah

20 hour rate (0.16 A, 5.25 V)

Average weight: 0.65 kg

Dimensions: 134*34*62*67 (mm)

Operating temperature:

Discharge -20~60 °C

Charge -10~60 °C

Storage -20~60 °C

Recommended storage temperature:

0 °C ~ 25 °C, no more than 6 months



