

Model number: VC-12713955

Type designation: VRLA

Chemical system: AGM Technology

Number of cells: 6

Internal resistance: Fully Charged battery 77 °F (25 °C) 55 mOhms

Self-discharge: 3 % of capacity declined per month at 20 °C (average)

Short circuit current: 60 A

Energy content: 14.4 Wh

Nominal Voltage: 12 V

Nominal Capacity: 1.2 Ah

20 hour rate (0.06 A, 10.5 V)

Average weight: 0.53 kg

Dimensions: 97*43*52*58 (mm)

Operating temperature:

Discharge -20~60 °C

Charge -10~60 °C

Storage -20~60 °C

Recommended storage temperature:

0 °C ~ 25 °C, no more than 6 months



