

Model number: VC-12713975

Type designation: VRLA

Chemical system: AGM Technology

Number of cells: 6

Internal resistance: Fully Charged battery 77 °F (25 °C) 14 mOhms

Self-discharge: 3 % of capacity declined per month at 20 °C (average)

Short circuit current:850 A

Energy content: 204 Wh

Nominal Voltage: 12 V

Nominal Capacity: 17 Ah

20 hour rate (0.85 A, 10.5 V)

Average weight: 5.5 kg

Dimensions: 181*77*167*167 (mm)

Operating temperature:

Discharge -20~60 °C

Charge -10~60 °C

Storage -20~60 °C

Recommended storage temperature:

0 °C ~ 25 °C, no more than 6 months



