

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.



23A ALKALINE BATTERY

Item No.:	Pcs per pack
2542825	1
3221595	4


TECHNICAL DATA

Type:	23A
Classification:	Non-rechargeable
Chemical system:	Zn/KOH-H ₂ O/MnO ₂
Nominal voltage:	12.0 V
Weight (approx.):	7.9 g
Capacity:	55 mAh
Loading:	20 kΩ (20 ± 2 °C, < 75% RH)
Cut-off voltage:	6.0 V
Operating conditions:	-18 to +50 °C, 55 ± 20 % RH recommended +10 to +35 °C
Storage conditions:	20 ± 2 °C, 55 ± 20 % RH
Heavy metals:	No added mercury (Hg), Cadmium (Cd), or Lead (Pb)

For performance and safety, observe the operating / storage conditions. Capacity varies depending on the applied load, temperature, and cut-off voltage.




DIMENSIONS (mm)



/	min	max
Ø	9.7	10.3
A	27.5	28.5
F	3.5	6.0

DISCHARGE PERFORMANCE



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2025 by Conrad Electronic SE.

*2542825_3221595_v1_0425_02_ds_en