
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A0	INITIAL RELEASE	2026.01.16	





NOTE:
RATING VOLTAGE:230VAC 50/60HZ
RATING CURRENT:16A
MAX. CURRENT:16A
MAX. POWER:3680W
SUPPORT :IP20
RoHS(2011/65/EU) and (2015/863/EU) and REACH COMPLIANT

Item#	Length (m)	Tolerance (mm)
19.07.1072	1.5	50
19.07.1073	3	50

NO.	PART NAME	DESCRIPTION	QUANTITY	REMARKS
⑤	SOCKET	CEE 7/3 GERMAN SOCKET	3	
④	PLUG	CEE 7/7 GERMAN PLUG	1	
③	PLASTIC	PP,BLACK	1	
②	HOUSING	PP, BLACK	1	
①	CABLE	H05VV-F3G×1.5mm² COPPER,BLACK PVC JACKET	1	

ITEM NO.	19.07.1072, 19.07.1073
LENGTH	See above table
NAME	ROLINE Power Strip, 6way, 45°, black

SECOMP

MAPE		
DRAW BY	SCALE	MM
	PAGE	1/1