

QU-POS-170

Wireless Payment Terminal

- 2.8 Inch large color screen, support electronic signature
- Support payment methods: Magnetic Card Reader
IC Card Reader ,NFC,QR code
- Support WiFi ,GPRS, 3G



Bank Card



NFC



Printer



1D/2D QR
Code Reader



E-Signature



QU-POS-170

Specifications



NFC



Bank Card



CPU

32-bit secure CPU, ARM11

Card Reader

Magnetic Card Reader
Smart Card Reader
Contactless Card Reader

Peripheral Port

1 * Mini USB
Supports charging and
USB 2.0, OTG

Working Environment

Temperature:
0°C~50°C(32°F~122°F);
Humidity:
10%~90% (non-condense)

Certification

PCI PTS 5.x, EMV Level 1&2,
EMV Contactless L1, UnionPay
CCC, CE, FCC, RoHS, JCB
Expresspay, Paywave, Paypass

Memory

128MB FLASH
64MB SDRAM

Barcode Reader (optional)

Reads 1D & 2D Codes

Printer

Thermal printer
Paper Width: 58mm
Diameter: 40mm

Storage Environment

Temperature:
-20°C ~ 60°C(-4°F~140°F)
Humidity:
5%~95% (non-condense)

Weight

356g

Display

2.8 inch, 320*240 TFT LCD

Card Slots

1/2 SAM
1 SIM

Power Supply

Input: 100 ~ 240VAC, 50Hz/60Hz
Output: 5 VDC, 1A

Optional

backup battery
car jack charger,
dock charger

Keypad

10 alphanumeric keys
8 function keys
1 power switch key

Communication

GPRS,
Optional 3G (WCDMA)
Optional WiFi

Li-polymer Battery

2600mAh, 3.7V

Dimensions

170*85*55mm



The configuration and parameters listed on the product page above are subject to the actual product and are subject to change without notice.

Tel: +49 (0) 202 404329 Fax: +49 (0) 202 404350 E-mail: kontakt@quio-rfid.de Web: www.quio-rfid.de